Satisfy Professional's Needs



# Cordless Cooler & Warmer Box CW002G / CW001G / CW003G





# -18°C~60°C [0°F~140°F]





# -18°C~60°C [0°F~140°F]





Freeze the ice pack



**Cool the drink** 

Warm the caulk tube

Caulk tubes to be warmed must be brand new and unopened. Also caulk tubes must be stored in the box within the storage temperature range recommended by the manufacturer of caulk tubes.\*

\*Do not store opened caulk tubes with foods because they produce volatile gas.

## Compatible with 4 power sources



\*Also can be powered by the combination of one XGT battery and one LXT battery. (CW002G/CW001G only)



### **CW002G**

#### The large capacity of 50L, which can be used by multiple persons, enables to keep a lot of items cold or hot.



About 15 x 2L PET bottles can be stored vertically.

#### Work amount on full battery charge




**Inner tray** 

5°C [40°F] about 19.5 h

Top cover with damper function



Enables to make the most of the inside top space of the box to store small items.



60°C [140°F] about

4.5 h

Softly closes to minimize the chance storage box, open of injury even if you release your hand.



1/4 LXT battery port

2/3 XGT battery port

When cleaning the the cap to drain water from the box.





transportation on casters.



#### The same features and benefits as those of CW001G/CW003G









Able to store up to four 2L plastic bottles or twenty 500mL plastic bottles.

Work amount on full battery charge with two BL4040 batteries

-18°C [0°F]	5°C [40°F]	60°C [140°F]
about	about	about
<b>8</b> h	22.5 h	/ <b>n</b>



2/3 XGT battery port



### **CW003G**

**Compact design** 


about

Convenient size for one to several people.



Able to store six 500mL plastic bottles vertically (up to 220mm in height).

#### Work amount on full battery charge



LXT battery port

2 XGT battery port




By attaching optional Shoulder belt, you can also hang this box on your shoulder.







#### Comfort/Lifestyle



## Cordless Cooler & Warmer Box

CW002G / CW001G / CW003G

 
 CW002G

 Capacity
 50 L (13.2 gal)

 Cooling system
 Compressor

 Cooling Capacity
 -18/-15/-10/ (0/5/15/25/

 Warming system
 Heater

 Warming capacity
 30/35/40/4

 (B5/95/105/
 Run Time (hrs)

 W/LBL4040 M
 Cord Length

 AC Adapter / C
 Dimensions (L x W x H)

 867 x 465 x 47.
 Net weight

Compressor -18/-15/-10/-5/0/5/10°C (0/5/15/25/30/40/50°F) Heater 30/35/40/45/50/55/60°C (85/95/105/115/120/130/140°F) w/BLBL4040X2,-18/5/60°C:8/19.5/4.5 AC Adapter / Cigar Socket Cable: 2/2.5 m (6.5/8.2 ft) 867x 465 x 476 mm (34-1/8 x 18-1/4 x 18-3/4") 25.6 - 29.0 kg (56.4 - 63.9 lbs.)

Compression -18/-15/-10/-5/0/5/10°C (0/5/15/25/30/40/50°F) Heater 30/35/40/45/50/55/60°C (85/95/105/115/120/130/140°F) w/BLBL4040X2,-18/5/60°C:8/22.5/7 AC Adapter/Cigar Socket Cable: 2/2.5 m (6.5/8.2 ft) 633 x 341 x 372 mm (26-1/8 x 13-3/8 x 14-5/8") 13.8 - 17.3 kg (30.4 - 38.1 lbs.)

CW001G

20 L (5.3 gal)

Compressor

CW003G

7 L (1.8 gal) Compressor -18/-15/-10/-5/0/5/10°C (0/5/15/25/30/40/50°F) Heater 30/35/40/45/50/55/60°C (85/95/105/115/120/130/140°F) w/BLBL4040,-18/5/60°C:5.5/13.5/5.5 AC Adapter / Cigar Socket Cable: 2/2.5 m (6.5/8.2 ft) 456 x 245 x 308 mm (18 x 9-5/8 x 12-1/8") 7.9-9.4 kg (17.4-20.7 lbs.)

Standard Equipment : Shoulder Belt (CW001G / CW003G), AC Adaptor (Country-specific), Cigar Socket Cable

Not covered by EPTA-Procedure

Items of standard equipment and specifications may vary by country or area.

# Makita Corporation

3-11-8 Sumiyoshi-cho, Anjo, Aichi, 446-8502 Japan